

TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Toolbag, with laptop and document compartment, equipped with: cable cutter, diagonal cutter, stripping pliers, insulation stripper, crimp tool set, combination, needle-nose, and water pump pliers, VDE screwdriver bladed: 0.4 x 2.5/0.5 x 3.0/1.0 x 4.0/1.0 x 6.5 crosshead: PHO/PH1/PH2, control cabinet key, voltage tester, ferrule box, blades, tape measure, toolbag



Your advantages

- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range
- Rugged and heavy-duty tool bags

Commercial data

Item number	1212504
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4046356528405
Weight per piece (including packing)	7,600 g
Weight per piece (excluding packing)	7,600 g
Customs tariff number	82060000
Country of origin	DE

TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

Set consists of

CUTFOX 25 VDE - Cable-cutting tool

1212127

<https://www.phoenixcontact.com/us/products/1212127>

Cable cutter, precision blade with macro-notching, for copper and aluminum up to 70 mm², VDE 1000 V AC/ 1500 V DC tested



CUTFOX-S VDE - Diagonal cutter

1212207

<https://www.phoenixcontact.com/us/products/1212207>

Diagonal cutter for hard (piano wire) and soft wires, VDE 1000 V AC/1500 V DC tested



TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/us/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



CRIMPFOX-M SET - Crimping pliers set

1212093

<https://www.phoenixcontact.com/us/products/1212093>

Crimping pliers set, consisting of CRIMPFOX-M (pliers) and dies for insulated cable lugs 0.5 ... 2.5 mm² (1212074), non-insulated conduit lugs 0.5 ... 6 mm² (1212079) and ferrules 0.25 ... 10 mm² (1212080) and 16/25 mm² (1212081).



UNIFOX-C VDE - Combination pliers

1212202

<https://www.phoenixcontact.com/us/products/1212202>

Combination pliers, notched gripping surface, VDE 1000 V AC/1500 V DC tested, size: 180 mm



TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

UNIFOX-P VDE - Needle-nose pliers

1212204

<https://www.phoenixcontact.com/us/products/1212204>

**Needle-nose pliers with blade, notched grip area,
VDE 1000 V AC/1500 V DC tested**



UNIFOX-WP - Water pump pliers

1212365

<https://www.phoenixcontact.com/us/products/1212365>

**Water pump pliers, with groove joint, grip areas with dual notching, acc. to
VDE ISO 8976**



TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



SZS 0,4X2,5 VDE - Screwdriver

1205037

<https://www.phoenixcontact.com/us/products/1205037>

Screwdriver, slot-headed, VDE insulated, size: 0.4 x 2.5 x 80 mm, 2-component grip, with non-slip grip



SZS 0,5X3,0 VDE - Screwdriver

1207404

<https://www.phoenixcontact.com/us/products/1207404>

Screwdriver, slot-headed, VDE insulated, size: 0.5 x 3.0 x 100 mm, 2-component grip, with non-slip grip



TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



SZS 1,0X4,0 VDE - Screwdriver

1205066

<https://www.phoenixcontact.com/us/products/1205066>

Screwdriver, slot-headed, VDE insulated, size: 1.0 x 4.0 x 100 mm, 2-component grip, with non-slip grip



SZS 1,0X6,5 VDE - Screwdriver

1205079

<https://www.phoenixcontact.com/us/products/1205079>

Screwdriver, slot-headed, VDE insulated, size: 1.0 x 6.5 x 150 mm, 2-component grip, with non-slip grip



TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

SZK PH0 VDE - Screwdriver

1205147

<https://www.phoenixcontact.com/us/products/1205147>

Screwdriver, PH crosshead, VDE insulated, size: PH 0 x 80 mm, 2-component grip, with non-slip grip



SZK PH1 VDE - Screwdriver

1205150

<https://www.phoenixcontact.com/us/products/1205150>

Screwdriver, PH crosshead, VDE insulated, size: PH 1 x 80 mm, 2-component grip, with non-slip grip



TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

SZK PH2 VDE - Screwdriver

1205163

<https://www.phoenixcontact.com/us/products/1205163>

Screwdriver, PH crosshead, VDE insulated, size: PH 2 x 100 mm, 2-component grip, with non-slip grip



DUSPOL EXPERT - Voltage tester

1209091

<https://www.phoenixcontact.com/us/products/1209091>

Voltage tester, for DC and AC voltages from 12 V to 1000 V AC/1000 V DC, IP65



TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



USS 4 - Control cabinet key

1203149

<https://www.phoenixcontact.com/us/products/1203149>

Control cabinet key, metal, for all common types of control cabinet



AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>

Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK



TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



TOOL-BAG EMPTY - Toolbag, unequipped

1212500

<https://www.phoenixcontact.com/us/products/1212500>

Tool bag, with document and laptop compartments, unequipped



TOOL-BAG - Tool set



1212504

<https://www.phoenixcontact.com/us/products/1212504>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Bag

Dimensions

Width	225 mm
Height	340 mm
Depth	225 mm
Length	410 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 9.0	EC000149
----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

TOOL-BAG - Tool set

1212504

<https://www.phoenixcontact.com/us/products/1212504>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com