

UNIFOX-PE VDE - Needle-nose pliers



1212529

<https://www.phoenixcontact.com/us/products/1212529>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Needle-nose pliers, angled design, with opening spring and locking device, finely notched grip area, stripping possible for 1.5 mm² and 2.5 mm², integrated M8 - M10 ring wrench, VDE 1000 V AC/1500 V DC tested

Your advantages

- Individually tested safety tools according to DIN EN 60900 (VDE 0682-201)
- Notched gripping surface and sharp cutting edge
- Ergonomically shaped two-component handles for fatigue-free and non-slip use
- VDE tested

Commercial data

Item number	1212529
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3162
GTIN	4046356589574
Weight per piece (including packing)	291.9 g
Weight per piece (excluding packing)	291 g
Customs tariff number	82032000
Country of origin	DE

UNIFOX-PE VDE - Needle-nose pliers

1212529

<https://www.phoenixcontact.com/us/products/1212529>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Universal tools
Application	Aluminum
Product property	Copper
	Cutting edge is inductively hardened
	Finely notched gripping surface
	Angled, ergonomic shape
	Ergonomic two-component handle
	Spring reset with locking mechanism
	Special tool steel, die-forged and oil-hardened\
	VDE tested

Dimensions

Length	200 mm
--------	--------

Material specifications

Color	black
-------	-------

Cable/line

External cable diameter	≤ 13.00 mm
-------------------------	------------

Standards and regulations

Tests	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5745

UNIFOX-PE VDE - Needle-nose pliers

1212529

<https://www.phoenixcontact.com/us/products/1212529>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212529>



EAC

Approval ID: RU x-DE.xx08.B.02974



VDE approval of drawings

Approval ID: 40052526

UNIFOX-PE VDE - Needle-nose pliers

1212529

<https://www.phoenixcontact.com/us/products/1212529>



Classifications

ECLASS

ECLASS-13.0	21043816
ECLASS-15.0	21043816

ETIM

ETIM 9.0	EC000835
----------	----------

UNSPSC

UNSPSC 21.0	27112100
-------------	----------

UNIFOX-PE VDE - Needle-nose pliers

1212529

<https://www.phoenixcontact.com/us/products/1212529>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com