

CRIMPFOX ZA 2_DB - Crimping pliers



1212815

<https://www.phoenixcontact.com/us/products/1212815>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules according to DIN 46228-1:1992-08 and DIN 46228-4:1990-09, type of packaging: with holder for sales display (backcard)

Commercial data

Item number	1212815
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356994804
Weight per piece (including packing)	297.083 g
Weight per piece (excluding packing)	297.083 g
Customs tariff number	82032000
Country of origin	DE

CRIMPFOX ZA 2_DB - Crimping pliers



1212815

<https://www.phoenixcontact.com/us/products/1212815>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Square crimp
Min. cross section	0.5 mm ²
Max. cross section	6 mm ²

Connection data

Conductor connection

Cross section range, metric

0.5 mm² ... 6 mm²

Dimensions

Length	195 mm
--------	--------

Material specifications

Color	black/green
Material	Steel with plastic handle

CRIMPFOX ZA 2_DB - Crimping pliers



1212815

<https://www.phoenixcontact.com/us/products/1212815>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212815>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX ZA 2_DB - Crimping pliers



1212815

<https://www.phoenixcontact.com/us/products/1212815>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX ZA 2_DB - Crimping pliers



1212815

<https://www.phoenixcontact.com/us/products/1212815>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com