

# PROT-M12 MS-M-CHAIN PPI - Sealing cap



1320659

<https://www.phoenixcontact.com/us/products/1320659>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

An M12 screw plug for the unoccupied M12 sockets of the shielded sensor/actuator cable, boxes and flush-type connectors



## Your advantages

- Reliable protection of unoccupied slots during transport and use in the field
- Protected against splash water and dust by the internal seal
- Easy assembly by hand or using a wrench

## Commercial data

Item number	1320659
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB27
Product key	ABQZAB
GTIN	4063151605988
Weight per piece (including packing)	17.5 g
Weight per piece (excluding packing)	13.22 g
Customs tariff number	74198090
Country of origin	DE

# PROT-M12 MS-M-CHAIN PPI - Sealing cap



1320659

<https://www.phoenixcontact.com/us/products/1320659>

## Technical data

### Product properties

Product type	Protective cap
Thread type	M12

### Connection data

Tightening torque	0.4 Nm
-------------------	--------

### Material specifications

Material	CuZn/Ni (Chain)
Material for screw connection	Brass

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65 (When installed)
	IP67 (When installed)
	IP69K (When installed)

  

Ambient temperature (operation) (male connector/female connector)	-40 °C ... 85 °C
---	------------------

# PROT-M12 MS-M-CHAIN PPI - Sealing cap



1320659

<https://www.phoenixcontact.com/us/products/1320659>

## Classifications

### ECLASS

ECLASS-13.0	27440208
ECLASS-15.0	27440208

### ETIM

ETIM 9.0	EC002314
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# PROT-M12 MS-M-CHAIN PPI - Sealing cap



1320659

<https://www.phoenixcontact.com/us/products/1320659>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)