

CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electrician's scissors, high cutting performance thanks to micro-serrated cutting area, suitable for copper, aluminum, Kevlar fibers, and plastic, two-component non-slip soft-grip handles, ergonomic design, adjustable screw joint

Your advantages

- Microserration for high cutting performance
- Cutting edge made of stainless steel
- Adjustable screw joint
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212621 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH3116 |
| GTIN | 4046356641227 |
| Weight per piece (including packing) | 105 g |
| Weight per piece (excluding packing) | 105 g |
| Customs tariff number | 82033000 |
| Country of origin | TW |

CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>



Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

| | |
|------------------|--------------------------------|
| Product type | Cutting tool |
| Application | Aluminum |
| | Copper |
| | Kevlar fibers |
| | Plastic |
| Set comprises | 1405246 TF-SCRJ-POF KONF SET |
| Product property | Microserrated |
| | Ergonomic two-component handle |
| | Adjustable screw joint |

Connection data

| | |
|----------------------------------|-------------------|
| Conductor cross-section flexible | 6 mm ² |
|----------------------------------|-------------------|

Dimensions

| | |
|--------|--------|
| Width | 78 mm |
| Height | 20 mm |
| Length | 155 mm |

Material specifications

| | |
|-------|----------------------|
| Color | multicolored (RAL -) |
|-------|----------------------|

Cable/line

| | |
|-------------------------|-----------|
| External cable diameter | ≤ 8.00 mm |
|-------------------------|-----------|

CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212621>



EAC

Approval ID: RU x-DE.xx08.B.02974

CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21044701 |
| ECLASS-15.0 | 21044701 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000142 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CUTFOX-ES - Cutting tool

1212621

<https://www.phoenixcontact.com/us/products/1212621>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com