

1413134

<https://www.phoenixcontact.com/us/products/1413134>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-pos., PUR, halogen-free, shielded, black gray RAL 7021, free cable end, to straight M12 socket, A-coded, cable length: 27 m

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1413134       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 10 pc         |
| Product key                          | AF1CKA        |
| GTIN                                 | 4046356987905 |
| Weight per piece (including packing) | 1,359 g       |
| Weight per piece (excluding packing) | 1,359 g       |
| Country of origin                    | PL            |

# SAC-5P-27,0-PUR/M12FS SH - Sensor/actuator cable



1413134

<https://www.phoenixcontact.com/us/products/1413134>

## Technical data

### Product properties

|              |                       |
|--------------|-----------------------|
| Product type | Sensor/actuator cable |
|--------------|-----------------------|

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 48 V AC |
|                       | 60 V DC |

# SAC-5P-27,0-PUR/M12FS SH - Sensor/actuator cable



1413134

<https://www.phoenixcontact.com/us/products/1413134>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

# SAC-5P-27,0-PUR/M12FS SH - Sensor/actuator cable



1413134

<https://www.phoenixcontact.com/us/products/1413134>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)