

HC-B-GB-M32-ER-AL - Cable gland

1414665

<https://www.phoenixcontact.com/us/products/1414665>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Set consisting of: EVO metal adapter 1414258 and metal screw connection with bending armor rod 1415184, M32



Commercial data

Item number	1414665
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF57
Product key	AF7APM
GTIN	4055626031163
Weight per piece (including packing)	385.7 g
Weight per piece (excluding packing)	385.7 g
Customs tariff number	85389099
Country of origin	DE

HC-B-GB-M32-ER-AL - Cable gland

1414665

<https://www.phoenixcontact.com/us/products/1414665>



Technical data

Product properties

Product type	Cable screw gland
No. of conductors	1
Type of the screw connection	M32
Shielded	no

Dimensions

Dimensional drawing	
Wrench size, union nut	36 mm
Wrench size, support	36 mm

Material specifications

Color	brass color
Material Pressure screw	Brass, nickel-plated
Seal material	EPDM
Seal material O-ring	NBR
Material for screw connection	Brass, nickel-plated

Cable/line

External cable diameter Cable 1	13 mm ... 21 mm
---------------------------------	-----------------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 100 °C

HC-B-GB-M32-ER-AL - Cable gland


1414665

<https://www.phoenixcontact.com/us/products/1414665>



Drawings

Dimensional drawing



Dimensional drawing

HC-B-GB-M32-ER-AL - Cable gland

1414665

<https://www.phoenixcontact.com/us/products/1414665>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1414665>



EAC

Approval ID: RU C-DE.AI30.B.01102



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00387

HC-B-GB-M32-ER-AL - Cable gland

1414665

<https://www.phoenixcontact.com/us/products/1414665>



Classifications

ECLASS

ECLASS-13.0	27140801
ECLASS-15.0	27140801

ETIM

ETIM 9.0	EC000441
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

HC-B-GB-M32-ER-AL - Cable gland

1414665

<https://www.phoenixcontact.com/us/products/1414665>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	576f3017-497d-42b2-adb0-aedf4ac9f8a4

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com