

# A-INL-NPT1-N-S - Counter nut

1416012

<https://www.phoenixcontact.com/us/products/1416012>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, shielding: no, for threads 1"-NPT, color: silver-colored



## Commercial data

Item number	1416012
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4055626056135
Weight per piece (including packing)	40 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	74153300
Country of origin	IN

# A-INL-NPT1-N-S - Counter nut

1416012

<https://www.phoenixcontact.com/us/products/1416012>



## Technical data

### Product properties

Product type	Flat nut
Shielded	no
Thread type	1"-NPT

### Dimensions

Length	7 mm
Diameter	32.4 mm
Connecting thread diameter	32.4 mm
Wrench size, counter nut	41 mm
Hexagon angular dimension	45 mm
Thread type connection side	1"-NPT

### Material specifications

Material	Brass, nickel-plated
----------	----------------------

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-70 °C ... 220 °C
---------------------------------	-------------------

# A-INL-NPT1-N-S - Counter nut

1416012

<https://www.phoenixcontact.com/us/products/1416012>



## Classifications

### ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

### ETIM

ETIM 9.0	EC000879
----------	----------

### UNSPSC

UNSPSC 21.0	31161700
-------------	----------

# A-INL-NPT1-N-S - Counter nut

1416012

<https://www.phoenixcontact.com/us/products/1416012>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ce5a4075-e79d-470b-b7cf-1ca66b481278

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)