

# IV-AW6S - Terminal position assurance



1521023

<https://www.phoenixcontact.com/us/products/1521023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal position assurance, number of positions: 6, material: PA-GF



## Commercial data

Item number	1521023
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF72
Product key	AF2IEC
GTIN	4063151985059
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	1.6 g
Country of origin	MX

# IV-AW6S - Terminal position assurance

1521023

<https://www.phoenixcontact.com/us/products/1521023>



## Technical data

### Notes

General	AW6S
General	Use with AT06-6S housings

### Product properties

Product type	Terminal position assurance
Series	AT06
Number of positions	6

### Electrical properties

Nominal voltage $U_N$	50 V AC/DC (IEC rating)
-----------------------	-------------------------

### Dimensions

Dimensional drawing	
Width	18.2 mm
Height	18.3 mm
Length	20.9 mm

### Material specifications

Housing material	PA-GF
------------------	-------

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-55 °C ... 125 °C

# IV-AW6S - Terminal position assurance


1521023

<https://www.phoenixcontact.com/us/products/1521023>



## Drawings

Dimensional drawing



AW6S top view and side view

# IV-AW6S - Terminal position assurance

1521023

<https://www.phoenixcontact.com/us/products/1521023>



## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

# IV-AW6S - Terminal position assurance

1521023

<https://www.phoenixcontact.com/us/products/1521023>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)