


2201632

<https://www.phoenixcontact.com/us/products/2201632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



19" socket strip, color: green, number of positions: 32, product range: FRONT-ZFL 1,5, pitch: 5.08 mm, type of packaging: packed in cardboard

Commercial data

Item number	2201632
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AA08
Product key	AAHHBA
GTIN	4017918902001
Weight per piece (including packing)	55.47 g
Weight per piece (excluding packing)	55.09 g
Customs tariff number	85366990
Country of origin	CN

FRONT-ZFL 1,5/D32 - Female connector strip



2201632

<https://www.phoenixcontact.com/us/products/2201632>

Technical data

Product properties

Product type	19" socket strip
Product family	FRONT-ZFL 1,5
Type	D
Number of positions	32
Pitch	5.08 mm


Electrical properties

Rated surge voltage (II/2)	4 kV
----------------------------	------

Connection data

Connection method	Spring-cage connection
Stripping length	11 mm

Dimensions

Dimensional drawing	
Width	94.7 mm
Height	20.3 mm
Length	28.5 mm
Pitch	5.08 mm

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PBT
Contact surface	Tin Sn

Standards and regulations

Connection in acc. with standard	EN-VDE
----------------------------------	--------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

FRONT-ZFL 1,5/D32 - Female connector strip


2201632

<https://www.phoenixcontact.com/us/products/2201632>



Drawings

Dimensional drawing



FRONT-ZFL 1,5/D32 - Female connector strip



2201632

<https://www.phoenixcontact.com/us/products/2201632>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2201632>

 cULus Recognized Approval ID: E60425-20020920				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	4 A	24 - 16	-
D				
	300 V	4 A	24 - 16	-

FRONT-ZFL 1,5/D32 - Female connector strip



2201632

<https://www.phoenixcontact.com/us/products/2201632>

Classifications

ECLASS

ECLASS-13.0	27460101
ECLASS-15.0	27460101

ETIM

ETIM 9.0	EC002643
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FRONT-ZFL 1,5/D32 - Female connector strip



2201632

<https://www.phoenixcontact.com/us/products/2201632>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	4.793 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com