

# RM-12P1N121300 - Circular connector (cable-side)



1605042

<https://www.phoenixcontact.com/us/products/1605042>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## Commercial data

Item number	1605042
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356250108
Weight per piece (including packing)	72.25 g
Weight per piece (excluding packing)	72.25 g
Country of origin	DE

# RM-12P1N121300 - Circular connector (cable-side)



1605042

<https://www.phoenixcontact.com/us/products/1605042>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Number Contact (Contact group 1)	12
Diameter Contact (Contact group 1)	1 mm
Litz wire cross-section min. Contact (Contact group 1)	0.08 mm <sup>2</sup>
Litz wire cross-section max. Contact (Contact group 1)	1 mm <sup>2</sup>
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Material (Seal)	FPM
Degree of protection (plugged in)	IP65 IP67

# RM-12P1N121300 - Circular connector (cable-side)




1605042

<https://www.phoenixcontact.com/us/products/1605042>

## Drawings

Schematic diagram



Connector pin assignment


# RM-12P1N121300 - Circular connector (cable-side)



1605042

<https://www.phoenixcontact.com/us/products/1605042>

Schematic diagram



Dimensional drawing

# RM-12P1N121300 - Circular connector (cable-side)



1605042

<https://www.phoenixcontact.com/us/products/1605042>

## Classifications

### ETIM

ETIM 8.0	EC001121
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# RM-12P1N121300 - Circular connector (cable-side)



1605042

<https://www.phoenixcontact.com/us/products/1605042>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)