

FLKM 50-PA-HW/C300 - Front adapter

2322016

<https://www.phoenixcontact.com/us/products/2322016>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapters, for Honeywell C300, series C I/O, max. 1x 16 channels can be connected. (50-pos. FLK connector)

Commercial data

Item number	2322016
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK231H
GTIN	4046356448260
Weight per piece (including packing)	100 g
Weight per piece (excluding packing)	100 g
Customs tariff number	85369010
Country of origin	DE

FLKM 50-PA-HW/C300 - Front adapter

2322016

<https://www.phoenixcontact.com/us/products/2322016>



Technical data

Product properties

Product type	Front adapter
Insulation characteristics	
Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)
	4 A (per connection, supply via separate power supply)
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV

Supported controller HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDIL01 (non-redundant)
	TDOB01 (non-redundant)

Connection data

Field level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50
Pitch	2.54 mm

Supply

Connection method	Spring-cage connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

FLKM 50-PA-HW/C300 - Front adapter

2322016

<https://www.phoenixcontact.com/us/products/2322016>



Mounting

Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

FLKM 50-PA-HW/C300 - Front adapter




2322016

<https://www.phoenixcontact.com/us/products/2322016>

Drawings

Circuit diagram



Connection scheme: FLKM 50-PA-HW/C300

FLKM 50-PA-HW/C300 - Front adapter

2322016

<https://www.phoenixcontact.com/us/products/2322016>



Classifications

ECLASS

ECLASS-13.0

27242292

FLKM 50-PA-HW/C300 - Front adapter

2322016

<https://www.phoenixcontact.com/us/products/2322016>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
----------------------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com