

VISU+ 2 SP IEC 60870 104 - Visualization software

2404884

<https://www.phoenixcontact.com/us/products/2404884>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Driver license for IEC 60870-5-104. Only in conjunction with a valid Visu+ runtime license including driver connection (Visu+ RT-D).

Commercial data

Item number	2404884
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DRDADG
GTIN	4055626461014
Weight per piece (including packing)	102.6 g
Weight per piece (excluding packing)	39.82 g
Country of origin	DE

Technical data

Product properties

Product type	Visualization
Basic functions	Connection in accordance with IEC 60870-5-104 via TCP/IP as a client.

System properties

Intended use for the software	Visualization
-------------------------------	---------------

License information

Type of license	Driver license
-----------------	----------------

Functionality

Basic functions	Connection in accordance with IEC 60870-5-104 via TCP/IP as a client.
Number of I/O nodes	0

System requirements

Operating equipment	Keyboard, mouse
Operating system	Windows® XP (SP3)
	Windows® Vista Business
	Windows® 7 Professional SP1 (32-Bit/64-Bit)
	Windows® 7 Ultimate SP1 (32-Bit/64-Bit)
	Windows® 8 Professional (32-Bit/64-Bit)
	Windows® 8 Enterprise (32-Bit/64-Bit)
	Windows® Server 2003
	Windows® Server 2008
	Windows® Server 2008 R2
	Windows® 10 (32-Bit/64-Bit)
Hard disk memory	min. 1 GByte (recommended: 2 GB)
Supported browsers	Internet Explorer 5.5 or higher
Languages supported	German, English, French, Italian
Optical drive	DVD-ROM
Screen resolution	1024 x 768 pixel(s) (XGA)

Classifications

ECLASS

ECLASS-13.0	27242502
ECLASS-15.0	27242502

ETIM

ETIM 9.0	EC001416
----------	----------

UNSPSC

UNSPSC 21.0	43231500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com