

EMD-SL-PS- 24AC - Power module



2866103

<https://www.phoenixcontact.com/us/products/2866103>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power modules, pluggable, for EMD-SL-..., supply voltage: 20.2...26.4 V AC

Your advantages

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front

Commercial data

Item number	2866103
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK663Z
GTIN	4017918952709
Weight per piece (including packing)	47 g
Weight per piece (excluding packing)	46.4 g
Customs tariff number	85043180
Country of origin	DE

EMD-SL-PS- 24AC - Power module

2866103

<https://www.phoenixcontact.com/us/products/2866103>



Technical data

Product properties

Product type	Power module
--------------	--------------

Input data

Input voltage	24 V AC (50/60 Hz)
Input voltage range AC	20.2 V AC ... 26.4 V AC

Dimensions

Width	32 mm
Height	35 mm
Depth	16 mm
Horizontal pitch	1.8 Div.

Material specifications

Housing material	Plastic
------------------	---------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

EMD-SL-PS- 24AC - Power module



2866103

<https://www.phoenixcontact.com/us/products/2866103>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

EMD-SL-PS- 24AC - Power module



2866103

<https://www.phoenixcontact.com/us/products/2866103>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com