

# UMK-SE 11,25-1 PROFIL - Lateral element

2975955

<https://www.phoenixcontact.com/us/products/2975955>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, Lateral element, profile width (internal): 72.2 mm, profile width (external): 77 mm, length: 11.25 mm



## Commercial data

Item number	2975955
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDCA
GTIN	4017918117542
Weight per piece (including packing)	5.86 g
Weight per piece (excluding packing)	5.76 g
Customs tariff number	39162000
Country of origin	PL

# UMK-SE 11,25-1 PROFIL - Lateral element

2975955

<https://www.phoenixcontact.com/us/products/2975955>



## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UMK
Product family	UMK SE
Ventilation openings present	no

### Dimensions

Length	11.25 mm
External dimensions	
Profile width (external)	77 mm
Internal dimensions	
Profile width (internal)	72.2 mm

### Material specifications

Color (Housing)	green (RAL 6021)
Material	PA
Flammability rating according to UL 94	V2
Surface characteristics	untreated

### Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)

# UMK-SE 11,25-1 PROFIL - Lateral element

2975955

<https://www.phoenixcontact.com/us/products/2975955>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2975955>



**UL Recognized**  
Approval ID: E240868

# UMK-SE 11,25-1 PROFIL - Lateral element

2975955

<https://www.phoenixcontact.com/us/products/2975955>



## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 9.0	EC002779
----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UMK-SE 11,25-1 PROFIL - Lateral element

2975955

<https://www.phoenixcontact.com/us/products/2975955>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)