

PRT/2 - Latching

3040631

<https://www.phoenixcontact.com/us/products/3040631>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Latching, can only be released using a screwdriver, width: 9 mm, height: 23.2 mm, number of positions: 2, color: orange

Commercial data

Item number	3040631
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE02
Product key	BE214Z
GTIN	4046356787765
Weight per piece (including packing)	0.602 g
Weight per piece (excluding packing)	0.584 g
Customs tariff number	39269097
Country of origin	PL

PRT/2 - Latching

3040631

<https://www.phoenixcontact.com/us/products/3040631>



Technical data

Product properties

Product type	Mounting material
Number of positions	2

Dimensions

Width	9 mm
Height	23.2 mm

Material specifications

Color	orange (RAL 2003)
Material	PA-GF
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

PRT/2 - Latching

3040631

<https://www.phoenixcontact.com/us/products/3040631>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PRT/2 - Latching

3040631

<https://www.phoenixcontact.com/us/products/3040631>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com