

FIP-3/3 SERVICE - Interruption plug



3069312

<https://www.phoenixcontact.com/us/products/3069312>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Interruption plug, nom. voltage: 400 V, nominal current: 20 A, color: red



Commercial data

Item number	3069312
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626157580
Weight per piece (including packing)	36.2 g
Weight per piece (excluding packing)	32 g
Customs tariff number	85366990
Country of origin	PL

FIP-3/3 SERVICE - Interruption plug



3069312

<https://www.phoenixcontact.com/us/products/3069312>

Technical data

Product properties

Product type	Plug
Number of positions	3
Pitch	8.2 mm

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated surge voltage	4 kV
Test surge voltage	5 kV

Connection data

Nominal current	20 A
Maximum load current	20 A
Nominal voltage	400 V

Dimensions

Width	24.5 mm
Height	53.4 mm
Pitch	8.2 mm

Material specifications

Color	red (RAL 3001)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

FIP-3/3 SERVICE - Interruption plug



3069312

<https://www.phoenixcontact.com/us/products/3069312>

Mounting type	Insertion in base strip
---------------	-------------------------

FIP-3/3 SERVICE - Interruption plug

3069312

<https://www.phoenixcontact.com/us/products/3069312>



Drawings

Circuit diagram



FIP-3/3 SERVICE - Interruption plug



3069312

<https://www.phoenixcontact.com/us/products/3069312>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FIP-3/3 SERVICE - Interruption plug



3069312

<https://www.phoenixcontact.com/us/products/3069312>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com