

EU5E-SWD-2A2A PXC - Input/output module



2903104

<https://www.phoenixcontact.com/us/products/2903104>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SmartWire DT™ analog module for connecting analog input/output signals, 2 inputs (0 - 10 V, 0 - 20 mA) and 2 outputs (0 - 10 V, 0 - 20 mA, can be configured individually).

Commercial data

Item number	2903104
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C470
Product key	DK7455
GTIN	4046356712675
Weight per piece (including packing)	114.6 g
Weight per piece (excluding packing)	114.6 g
Customs tariff number	85371091
Country of origin	DE

EU5E-SWD-2A2A PXC - Input/output module



2903104

<https://www.phoenixcontact.com/us/products/2903104>

Technical data

Product properties

Product type	Extension module
--------------	------------------

Input data

Input name	Analog inputs
Number of inputs	2

Connection data

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm² ... 1.5 mm²
Conductor cross-section flexible	0.2 mm² ... 1.5 mm²
Conductor cross-section AWG	24 ... 16

SmartWire™-DT

Connection method	Pin strip
Number of connections	1
Number of positions	8
Note	For SmartWire-DT device plug SWD4-8SF2-5 PXC

Interfaces

Data: SmartWire™-DT

Data rate	125 kBd / 250 kBd
Connection method	Pin strip, 8-pos.

Dimensions

Width	35 mm
Height	90 mm
Depth	101 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Standards and regulations

Standards/regulations	EN 50178
-----------------------	----------

Mounting

EU5E-SWD-2A2A PXC - Input/output module



2903104

<https://www.phoenixcontact.com/us/products/2903104>

Mounting type	DIN rail mounting
Mounting position	any

EU5E-SWD-2A2A PXC - Input/output module



2903104

<https://www.phoenixcontact.com/us/products/2903104>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com