

AH-ME - Covering hood

3240265

<https://www.phoenixcontact.com/us/products/3240265>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover, for the contact- and dust-protected encapsulation of the components



Your advantages

- The cover can be securely snapped onto the corresponding APH-ME end brackets and sealed as an option
- Cover profiles provide protection against unauthorized actuation of terminal strips
- This profile has been specially adapted to the shape of the test disconnect terminal blocks
- The AH-ME cover, which is enclosed on all sides, is snapped onto the end brackets and can be sealed as an option

Commercial data

Item number	3240265
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BE06
Product key	BE61ZX
GTIN	4046356462884
Weight per piece (including packing)	257.25 g
Weight per piece (excluding packing)	191.16 g
Customs tariff number	39269097
Country of origin	DE

AH-ME - Covering hood



3240265


<https://www.phoenixcontact.com/us/products/3240265>

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Dimensional drawing	
Width	150 mm
Height	200 mm
Depth	78 mm

Material specifications

Color	transparent
Material	PC
Flammability rating according to UL 94	V2
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

AH-ME - Covering hood


3240265

<https://www.phoenixcontact.com/us/products/3240265>



Drawings

Dimensional drawing



AH-ME - Covering hood



3240265

<https://www.phoenixcontact.com/us/products/3240265>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AH-ME - Covering hood



3240265
<https://www.phoenixcontact.com/us/products/3240265>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com