

# UMK 22 REL 24 VAC/21-21 - Active module



5520569

<https://www.phoenixcontact.com/us/products/5520569>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE relay module, fixed, 2PDT



## Commercial data

Item number	5520569
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y2
GTIN	4046356687737
Weight per piece (including packing)	53.3 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	MY

# UMK 22 REL 24 VAC/21-21 - Active module



5520569

<https://www.phoenixcontact.com/us/products/5520569>

## Technical data

### Notes

#### Trade restriction

CE note

The products are offered exclusively for export outside the EU and the European Economic Area.

### Product properties

Product type

Relay Module

### Input data

Nominal input voltage $U_N$	24 V AC
Input voltage range in reference to $U_N$	0.8 ... 1.1
Input voltage range	19.2 V AC ... 26.4 V AC

### Dimensions

Width	22.5 mm
Height	77 mm
Depth	50 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 9.0	EC001437
----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

5520569

<https://www.phoenixcontact.com/us/products/5520569>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-50  An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)