

WCC 18 - Cable clamp

3240253

<https://www.phoenixcontact.com/us/products/3240253>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable clamp, for DIN rails



Your advantages

- The cable clamps provide strain relief
- The halogen-free plastic troughs have been designed to be perfectly secure while simultaneously protecting the conductors
- Individual or bundled cables with a diameter of up to 18 mm can be installed safely and easily

Commercial data

Item number	3240253
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE74
Product key	BE7421
GTIN	4046356464550
Weight per piece (including packing)	37.58 g
Weight per piece (excluding packing)	37.37 g
Customs tariff number	73269098
Country of origin	CN

WCC 18 - Cable clamp



3240253


<https://www.phoenixcontact.com/us/products/3240253>

Technical data

Product properties

Product type	Cable feed-through
--------------	--------------------

Dimensions

Dimensional drawing	
Wrench size	10 mm
Wrench size for mounting	10 mm

Material specifications

Material	Steel
Coating	galvanized

Cable/line

External cable diameter	12 mm ... 18 mm
-------------------------	-----------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

WCC 18 - Cable clamp


3240253

<https://www.phoenixcontact.com/us/products/3240253>



Drawings

Dimensional drawing



WCC 18 - Cable clamp

3240253

<https://www.phoenixcontact.com/us/products/3240253>



Classifications

ECLASS

ECLASS-13.0	23159090
ECLASS-15.0	23159090

ETIM

ETIM 9.0	EC011571
----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

WCC 18 - Cable clamp

3240253

<https://www.phoenixcontact.com/us/products/3240253>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com