

## Full-Motion Universal Tablet Desk Clamp for 7 in. to 10 in. Tablets

MODEL NUMBER: DDR0710SC



Mount your tablet above or below the surface of your desk, table or workstation to free up valuable space. Customize the tablet's angle and height for comfortable viewing.

### Description

The DDR0710SC Full-Motion Universal Tablet Desk Clamp attaches to your desk, table or workstation, allowing you to mount your tablet above or below it and free up valuable workspace. Upside-down mounting to a cabinet or workstation lets you read recipes or instructions at eye level. Clamps firmly to most flat surfaces up to 1.6 inches thick. Flexible arm lets you adjust your tablet's angle and height to fit your environment and comfort level. Fits tablets ranging from 7 to 10 inches. Rotates 360°, so you can view your tablet in portrait and landscape orientations. Easy installation in seconds with no tools necessary. Supports tablets up to 2.2 lbs (1 kg).

### Features

#### Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces up to 1.6 in. thick
- Fits most tablets from 7 to 10 in.
- Mounts above or below your workspace's surface
- Upside-down mounting lets you read recipes or instructions at eye level
- Flexible arm lets you adjust height and angle for comfortable viewing
- Full 360° rotation in both portrait and landscape orientations

#### Installs in Seconds

- No tools necessary
- Supports up to 2.2 lbs (1 kg)

## Specifications

OVERVIEW	
UPC Code	037332190543

### Highlights

- Clamps to most flat surfaces up to 1.6 in. thick
- Fits most tablets ranging from 7 to 10 in.
- Attaches above or below your workspace's surface
- Rotates 360° in portrait and landscape orientations
- Supports up to 2.2 lbs (1 kg)

### Package Includes

- DDR0710SC Full-Motion Universal Tablet Desk Clamp
- Installation instructions



Powering Business Worldwide

TRIPP LITE  
SERIES

Device Compatibility	Tablet
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Metal, Plastic
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	-180/+180 Tilt; 360 Swivel; 360 Rotate
Minimum Screen Size (in.)	7
Minimum Screen Size (cm)	17.78
Maximum Screen Size (in.)	10
Maximum Screen Size (cm)	25.4
Maximum Weight Capacity (lbs.)	2.2
Maximum Weight Capacity (kg)	1
Shipping Dimensions (hwd / in.)	3.15 x 8.26 x 11.42
Shipping Dimensions (hwd / cm)	8.00 x 20.98 x 29.01
Shipping Weight (lbs.)	1.72
Shipping Weight (kg)	0.78
Unit Dimensions (hwd / in.)	7.170 x 9.610 x 2.750
Unit Dimensions (hwd / cm)	18.21 x 24.42 x 6.99
Unit Weight (lbs.)	1.28
Unit Weight (kg)	0.58
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	No
Tools Necessary	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; RoHS3; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.