

Cisco Console Rollover Cable Adapter (RJ45 M/F) - Blue, 5 in.

MODEL NUMBER: N034-05N-BL



Converts a standard Ethernet cable into a serial rollover cable for connecting to Cisco or other hardware that requires rolled cables.

Features

Rollover Console Cable Converts a Straight-Through Ethernet Cable to a Rollover Cable This Cisco console rollover cable connects to the end of any standard RJ45 Ethernet cable and internally rolls the pins to convert the cable from straight through to rollover. This allows you to create a rollover connection between a computer terminal and the RJ45 console port on a Cisco modem, router, firewall, switch or other serial-based device without having to buy new cabling.

Provides Unrestricted Access to Adjacent Ports In contrast to short M/F plugs that block adjacent RJ45 ports when they are connected, this RJ45 rollover console cable for Cisco products is recommended for console servers and other devices where ports tend to be tightly packed together. The narrow RJ45 male end connects securely to the device, while leaving adjacent ports accessible.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This five-inch Cisco console rollover adapter features a blue PVC jacket and fully molded blue ends. The color-coding allows easy, fast identification in a crowded switch or router and helps prevent the cable from becoming inadvertently disconnected.

Highlights

- Connects to any standard RJ45 patch cable to create a rollover connection
- Internally rolls the pins to convert straight-through cable to rollover cable
- Narrow male RJ45 plug connects to device without blocking adjacent ports
- Color-coded blue for fast, easy identification in a crowded switch or router
- Recommended for Cisco modems, routers, switches and other serial devices

Applications

- Connect devices like Cisco switches, routers or other hardware that require rolled cables to an Ethernet network
- Change ports on a network device from straight-through to Cisco rollover

System Requirements

- Cisco or other network hardware using RJ45 serial ports that requires rolled cables

Package Includes

- N034-05N-BL Cisco Console Rollover Cable Adapter, Blue, 5-in. (12.7 cm)

Specifications

OVERVIEW	
UPC Code	037332236265
Technology	Cat5/5e; Cat6
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Blue
Cable Jacket Color	Blue
Cable Outer Diameter (OD)	0.81 +/- 0.05mm
Cable Length (in.)	5
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 158°F (-10° to 70°C)
Storage Temperature Range	5° to 176°F (-15° to 80°C)
Relative Humidity	0-90% non-condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.