

USB (2-in-1) Cable Kit for NetDirector KVM Switch B020-Series and KVM B022-Series, 19 ft. (5.79 m)

MODEL NUMBER: **P776-019**



Highlights

- Connects a USB Computer to B020- and B022-Series KVM Switches
- Makes management and organization of cables much easier
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable and a USB A Male cable
- Molded, color-coded connectors

System Requirements

A B020- or B022-Series KVM switch

Package Includes

- P776-019 19-ft. (5.79 m) KVM Switch USB (2-in-1) Cable Kit

Description

This USB (2-in-1) KVM cable kit is designed to connect a USB computer to B020- and B022-Series KVM Switches. The KVM Switch side of the cable kit consists of a HD15 Male cable. The computer side of the cable kit consists of a HD15 Male cable and a USB-A Male cable. This low-profile cable is incredibly flexible, making cable management a breeze. All cables are manufactured from superior molded cable with integral strain relief and foil shielding for maximum EMI/RFI protection.

Features

- Connects a USB computer to B020- and B022-Series KVM Switches
- KVM Switch side of the cable kit consists of a HD15 Male cable
- Computer side of the cable kit consists of a HD15 Male cable and a USB A Male cable
- Provides superior performance and cable management
- Molded ends with easy-grip textured overmold
- Low profile cable is super flexible and easy to control
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection

Specifications

OVERVIEW	
UPC Code	037332147080
Accessory Type	Cable Kit
Technology	VGA/SVGA
Accessory Class	KVM Switch Accessories
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	19
Cable Length (m)	5.79
Shipping Dimensions (hwd / in.)	0.50 x 6.00 x 8.00
Shipping Dimensions (hwd / cm)	1.27 x 15.24 x 20.32
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.