


M.2 NGFF PCIe SSD (M-Key) PCI Express (x4) Card

MODEL NUMBER: **PCE-1M2-PX4**



Increases your data transfer speed and internal storage by adding an M.2 PCIe-based solid state drive (M-Key) via your computer's PCIe expansion slot.

Description

The high-performance PCE-1M2-PX4 M.2 NGFF PCIe SSD (M-Key) PCI Express Card enhances your computer's speed and increases the amount of internal storage by adding an M.2 PCI Express (PCIe) SSD (M-Key) drive. You can add an ultra-fast four-lane M.2 SSD, such as a Samsung 950 Pro or Samsung SM 951, to a computer or server with an available x4, x8 or x16 PCI Express expansion slot. This lets you keep your operating system on your M.2 PCIe drive, while using larger platter drives for bulk storage. Its plug-and-play design requires no software, driver or external power supply, so setting up the card is easy enough. Just connect your drive to the PCE-1M2-PX4, and insert the unit inside your computer's PCIe expansion slot. The PCE-1M2-PX4 supports 2242, 2260 and 2280 M.2 drive types up to 80 millimeters. It's compatible with PCIe 3.0 motherboards and backward compatible with PCIe 2.0 and PCIe 1.0. Works with Windows and Mac computers.

Features

Adds M.2 PCIe-Based SSD (M-Key) to Your Computer's PCIe Expansion Slot

- Increases computer speed and internal storage
- Keep OS on M.2 PCIe drive and use larger platter drive for bulk storage
- PCIe 4-lane (x4) interface compatible with x4, x8 and x16 PCIe expansion slots
- Supports 2242, 2260 and 2280 M.2 drive types
- Works with PCIe 3.0 motherboards
- Backward compatible with PCIe 2.0 and PCIe 1.0
- Plug and play—no software, drivers or power supply needed
- Compatible with Windows (XP and later) and Mac (OS X 10.0 and later)

Specifications

Highlights

- Compatible with x4, x8 and x16 PCIe expansion slots
- Supports 2242, 2260 and 2280 M.2 drive types
- Works with PCIe 3.0 motherboards
- Backward compatible with PCIe 2.0 and PCIe 1.0
- Plug and play—no software, drivers or power supply needed

System Requirements

- Computer with PCIe expansion slot (x4, x8, x16)
- M.2 NGFF PCIe drive with M-Key or B+M-Key connector (not compatible with M.2 NGFF SATA SSDs)
- Supports 2242, 2260 and 2280 M.2 drive types
- Windows® (XP and later) or Mac® (OS X 10.0 and later) operating system

Package Includes

- PCE-1M2-PX4 M.2 NGFF PCIe SSD (M-Key) PCI Express Card
- (2) Screws
- SSD standoff nut
- Owner's manual

OVERVIEW

UPC Code

037332201287



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	PCIe
CONNECTIONS	
Number of Ports	1
PHYSICAL	
Color	Silver
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	1.06 x 6.50 x 4.92
Shipping Dimensions (hwd / cm)	2.69 x 16.51 x 12.50
Shipping Weight (lbs.)	0.12
Shipping Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	50° to 122°F (10° to 50°C)
Operating Humidity Range	10% to 80% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.