

Bracket Accessory - enables Vertical PDU Installation with Rear-Facing Outlets

MODEL NUMBER: PDUMVROTATEBRKT



Highlights

- Set of brackets enables vertical PDU placement with outlets facing the rear in button-mount equipped racks
- Rear facing outlets enhance airflow and equipment cabling access
- Toolless mounting supported

Description

PDUMVROTATEBRKT enables toolless installation of select PDUs in 0U vertical orientation with rear-facing outlets to facilitate better rack front-to-rear airflow and equipment access. Pair of brackets with installation buttons snap into the accessory mounting rails in equipped racks. Each bracket accepts a PDU button mount that snaps into place to securely hold a PDU as it distributes power to your rack enclosure.

Compatible with PDU1415, PDU1420T, PDU40TDUAL, PDUV15, PDUV20, PDUV30HV, PDUMV15, PDUMV20, PDUMV40, PDUMV30, PDUMV20HV, PDUMV30HV, PDUMV15NET, PDUMV20NET, PDUMV30NET, PDUMV20HVNET, PDUMV30HVNET and other PDUs referencing this accessory.

Features

- Enables toolless installation of select PDUs in 0U / vertical orientation with rear-facing outlets to facilitate better rack front-to-rear airflow and equipment access
- Pair of brackets with installation buttons snap into the accessory mounting rails in equipped racks
- Each bracket accepts a PDU button mount that snaps into place to securely hold a PDU as it distributes power to your rack enclosure
- Compatible with PDU1415, PDU1420T, PDU40TDUAL, PDUV15, PDUV20, PDUV30HV, PDUMV15, PDUMV20, PDUMV40, PDUMV30, PDUMV20HV, PDUMV30HV, PDUMV15NET, PDUMV20NET, PDUMV30NET, PDUMV20HVNET, PDUMV30HVNET and other PDUs referencing this accessory

Specifications

OVERVIEW	
UPC Code	037332147271
Accessory Type	Mounting Bracket
Accessory Class	PDU Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.70 x 3.65 x 2.10



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	6.86 x 9.27 x 5.33
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
Unit Dimensions (hwd / in.)	2.613 x 2.322 x 1.654
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.