

UPS Replacement Battery Cartridge for SUINT1000LCD2U UPS System, 24V

MODEL NUMBER: RBC24S



UPS backup battery replacement breathes new life into a Tripp Lite UPS system suffering from expired or weak internal batteries.

Features

UPS Replacement Battery Cartridge for SUINT1000LCD2U UPS System

This UPS backup battery replacement is carefully screened and certified to meet or exceed original specifications. The leakproof, no-maintenance RBC24S comes pre-assembled and pre-wired as two 12V batteries for quick and easy installation in your SUINT1000LCD2U. It functions within a wide range of operating temperatures. A sensor automatically informs the UPS that the battery has been replaced, so the UPS can reset the battery age. Reusable packaging allows you to easily send expired batteries to a recycling center.

Specifications

OVERVIEW	
UPC Code	037332239372
BATTERY	
DC System Voltage (VDC)	24
Included Battery Set	Contains (2) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 to 5 years typical, depending on UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.51 x 12.00 x 8.86
Shipping Weight (kg)	6.50
Unit Dimensions (hwd / in.)	2.640 x 5.950 x 7.910
Unit Dimensions (hwd / cm)	6.71 x 15.11 x 20.09

Highlights

- Replacement battery backup for SUINT1000LCD2U UPS system
- Carefully screened and certified to restore UPS runtime to original specs
- Leakproof internal battery requires no regular maintenance
- Ships fully assembled and ready for immediate installation to prevent downtime
- Auto-detection sensor allows UPS to reset internal battery age

Applications

- Replace the aging or expired internal battery in your Tripp Lite SUINT1000LCD2U UPS system

System Requirements

- Compatible with SUINT1000LCD2U UPS system

Package Includes

- RBC24S UPS Battery Replacement (pre-assembled battery pack with two 12V batteries)



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (lbs.)	14.33
Unit Weight (kg)	6.50
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.