


ZB 8,3 CUS - Zack marker strip



8191573

<https://www.phoenixcontact.com/us/products/8191573>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.3 mm, text field height: 8.3 mm, text field width: 10.5 mm

Commercial data

Item number	8191573
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4055626071701
Weight per piece (including packing)	2.044 g
Weight per piece (excluding packing)	2.044 g
Customs tariff number	49119900
Country of origin	US

ZB 8,3 CUS - Zack marker strip



8191573

<https://www.phoenixcontact.com/us/products/8191573>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	8.3 mm

Dimensions

Width	8.30 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	8.3 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap into tall marker groove
---------------	------------------------------

ZB 8,3 CUS - Zack marker strip



8191573

<https://www.phoenixcontact.com/us/products/8191573>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 8,3 CUS - Zack marker strip



8191573
<https://www.phoenixcontact.com/us/products/8191573>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com