


## Power Cable Kit for Healthcare Power Modules/Inverters/Chargers, 3 ft. (0.91 m)

MODEL NUMBER: HCBATTERYCABLE



Power cable kit connects a battery to a medical power module mounted on a mobile medical cart in a healthcare facility.

### Features

#### Power Cable Kit Connects a Battery to Your Medical Power Module

This cable is designed to work with medical power modules, including HC150SL, HCINT150SL, HC350SNR, HC350SR and HCINT350SNR. It includes a quick-release Anderson plug for easy connection to the power inverter/charger and three ring terminals for connecting to a Sealed Lead Acid (SLA) or Lithium Iron Phosphate (LiFePhos) battery. The wires (two 12 AWG red and one 10 AWG black) are three feet in length, but can be cut to a customized length to properly fit your application. Two user-replaceable 20-amp fuses are also included. This power cable kit accommodates 12VDC batteries up to 55Ah.

### Highlights

- Designed to work with select medical power modules
- Accepts 12VDC SLA or LiFePhos battery packs up to 55Ah
- Quick-release Anderson plug connects easily to power inverter/charger
- 3 ft. (0.91 m) cables can be easily cut to customized length and fitted with included ring terminals
- Includes 2 user-replaceable 20A fuses for immediate deployment

### Applications

- Supply battery power to a Tripp Lite power module connected to a mobile medical cart in a hospital or other healthcare facility

### System Requirements

- HC150SL, HCINT150SL, HC350SNR, HC350SR, HCINT350SNR and other compatible power modules

### Package Includes

- HCBATTERYCABLE Power Cable Kit, 3 ft.

## Specifications

| OVERVIEW               |                    |
|------------------------|--------------------|
| UPC Code               | 037332168771       |
| Accessory Type         | Cable Kit          |
| Country/Region         | Global             |
| Accessory Class        | UPS Accessories    |
| PHYSICAL               |                    |
| Color                  | Black; Red; Yellow |
| Cable Jacket Color     | Black; Red; Yellow |
| Power Cord Jacket Type | Null               |
| Number of Conductors   | 0                  |
| Cable Length (ft.)     | 3                  |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Length (m)                     | 0.91                      |
| Cable Length (in.)                   | 36                        |
| Cable Length (cm)                    | 914.4                     |
| Shipping Dimensions (hwd / in.)      | 1.00 x 2.50 x 3.50        |
| Shipping Weight (kg)                 | 0.25                      |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| High Voltage                         | No                        |
| Locking Plug                         | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.