


## Cable Ladder Runway E-Bend - 90 Degrees, 12 in. Width

MODEL NUMBER: **SRL90BEND12**



Creates a 90-degree curve for horizontal cable runway applications outside your enclosure or open frame rack.

### Features

**Cable Runway E-Bend Creates a 90-Degree Gradual Sweep for Horizontal Cable Ladder Runs**The SmartRack SRL90BEND12 allows you to place a curved right angle in your horizontal cable runway application. It connects to your 12-inch cable runway above your rack enclosure or open frame rack to allow flexibility in your overhead cable routing. Install it either parallel or perpendicular to the rack for clean, organized cable routing across an aisle or within a row.

**Measures 12 in. Wide with a 27 in. Wide Bend**This cable E-bend conforms to minimum-bend radius requirements (typically four times the cable diameter). It's made from lightweight tubular steel measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). It fits 12-inch (305-millimeter) cable runway widths, and meets Cat5e/6/6a requirements.

**Designed for Use with Rack Cabling Components**The SRL90BEND12 ships fully assembled for connecting right out of the package. It's compatible with 12-inch SRCABLELADDER and SRLBUTTSPLICE kit for toolless assembly. All accessories are sold separately.

### Highlights

- Routes bundles overhead to eliminate cable stress and cut cord clutter
- Installs parallel or perpendicular to rack to span aisles or spaces between racks
- Lightweight tubular steel construction designed to fit 12 in. cable runway widths
- Conforms to Cat5e/6/6a standards for high-density network applications
- Compatible with SmartRack® components for toolless assembly

### Applications

- Neatly bundle cable across an aisle or within a row of bayed racks in your data center

### System Requirements

- Works with SRCABLELADDER and SRLBUTTSPLICE

### Package Includes

- SRL90BEND12 Cable Ladder Runway E-Bend - 90 Degrees, 12 in. Width
- Installation guide

## Specifications

| OVERVIEW                        |                              |
|---------------------------------|------------------------------|
| UPC Code                        | 037332214515                 |
| Accessory Type                  | Cable Management Accessories |
| PHYSICAL                        |                              |
| Color                           | Black                        |
| Cable Jacket Color              | Black                        |
| Shipping Dimensions (hwd / in.) | 28.90 x 3.50 x 28.90         |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                          |
|-------------------------------------|--------------------------|
| Shipping Dimensions (hwd / cm)      | 73.41 x 8.89 x 73.41     |
| Shipping Weight (lbs.)              | 7.70                     |
| Shipping Weight (kg)                | 3.49                     |
| Unit Dimensions (hwd / in.)         | 26.960 x 26.960 x 50.500 |
| Unit Dimensions (hwd / cm)          | 68.48 x 68.48 x 128.27   |
| Unit Weight (lbs.)                  | 4.480                    |
| Unit Weight (kg)                    | 2.03                     |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                          |
| Product Compliance                  | RoHS                     |
| <b>WARRANTY &amp; SUPPORT</b>       |                          |
| Product Warranty Period (Worldwide) | 5-year limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.