


SmartRack 2U Mounting Rail Deep Adapter Kit for Server Racks, 4 in. (10.2 cm)

MODEL NUMBER: SRRAILDPTH2U



2U steel brackets increase or decrease mounting depth of rack equipment by 4 in.

Features

Increase or Decrease the Depth of Your Server Rack by 4 in.

This SmartRack® rail-depth adapter kit lets you mount rack equipment so that it either extends four inches (10.2 centimeters) past the front vertical mounting rails or recesses four inches within the rails. This would benefit you, for instance, if you mounted extra-deep equipment that protruded out the front of the rack and prevented you from closing the door. Or it can allow you easier access to front cabling and help cut down on cable strain.

Easy Installation Using the Included Hardware

The SRRAILDPTH2U comes with two steel mounting brackets made from heavy-duty steel with a black powder-coated finish to mesh seamlessly with your rack. Connect the 2U extension brackets to the front rails using the included hardware. Position the brackets outside the rails to increase rack depth or inside the rails to decrease rack depth. Then mount the equipment to the brackets. The SRRAILDPTH2U is compatible with EIA-standard 19-inch open frame racks and enclosures.

Highlights

- Adds 4 in. within your rack to provide extra room for deep equipment
- Can reduce mounting depth by 4 in. to allow easier front access to cabling
- Made from heavy-duty steel with a black powder-coated finish to match your rack
- Compatible with EIA-standard 19 in. open frame racks and enclosures
- 2U brackets come with all necessary mounting hardware for easy installation

System Requirements

Compatible with EIA-standard 19 in. open frame racks and rack enclosures

Package Includes

- (2) Adapter brackets
- (16) M6 screws
- (16) M6 cup washers
- (16) M6 cage nuts
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332263193
Product Type	Mounting Bracket
Accessory Type	Mounting Bracket; Rackmount Kit
Accessory Class	Rack Accessories
PHYSICAL	
Unit Dimensions (hwd / in.)	3.470 x 0.670 x 4.000
Unit Dimensions (hwd / cm)	8.814 x 1.702 x 10.160
Unit Weight (lbs.)	0.80



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (kg)	0.36
STANDARDS & COMPLIANCE	
Product Compliance	EIA/ECA-310-E; REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.