

HDMI to DVI Adapter Cable (M/M), 12 ft. (3.7 m)

MODEL NUMBER: **P566-012**

Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and DVI-enabled display.

Description

This DVI - HDMI cable allows interconnection between digital display devices, including HDTVs and projectors, to digital source devices, such as satellite/cable boxes, Blu-ray players and AV receivers. HDMI DTVs will display video received from existing DVI-equipped products, and DVI-equipped TVs will display video from HDMI sources. HDMI technology uses a much more compact and user-friendly connector than the existing DVI connector. The HDMI specification handles higher bandwidth, uncompressed video and multi-channel digital audio, all in one neat cable solution. (DVI-HDMI cable supports digital video only).

Features

- 12-ft. (3.66 m) DVI to HDMI Adapter Cable
- Creates a pure bi-directional digital connection between a DVI-enabled source and an HDMI-enabled display or an HDMI-enabled source and a DVI-enabled display.
- Gold plated connectors and contacts provide optimal signal transfer
- Premium Double-Shielded HDMI compliant cable protects against outside noise (EMI/RFI)
- Impedance matched twisted pair construction reduces cross-talk and interference
- Supports High-Definition (HD) video resolutions up to 1920 x 1080 @60Hz (1080p).

Specifications

| OVERVIEW | |
|--------------------------------|---------------------|
| UPC Code | 037332181329 |
| Product Type | Passive Cable |
| Technology | DVI; HDMI |
| VIDEO | |
| Max Supported Video Resolution | 1920 x 1200 (1080p) |

Highlights

- Premium double shielded digital video cable protects against EMI/RFI noise
- Gold plated connectors and contacts provide optimal signal transfer
- Supports high-def video resolutions up to 1920 x 1080 @ 60 Hz (1080p)
- Supports a bandwidth up to 5 Gbps

Package Includes

- 12-ft. (3.66 m) HDMI to DVI Gold Digital Video Cable (HDMI-M / DVI-M)



Powering Business Worldwide

TRIPP LITE
SERIES

| CONNECTIONS | |
|-------------------------------------|---------------------------|
| Side A - Connector 1 | HDMI (MALE) |
| Side B - Connector 1 | DVI-D SINGLE LINK (MALE) |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Length (ft.) | 12 |
| Cable Length (m) | 3.66 |
| Cable Length (in.) | 144 |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.55 |
| Shipping Weight (kg) | 0.25 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.