

3x 12V 9AH UPS Replacement Battery Cartridge Kit for Select Best, Powerware, Liebert and Other UPS

MODEL NUMBER: **RBC53**



Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range

Package Includes

- 3 12V UPS replacement batteries
- Instruction manual with installation, recycling and warranty information

Description

These premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety UPS brands and models. See the UPS replacement battery web page to confirm compatibility and quantity required.

Features

- Restore UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

Specifications

OVERVIEW	
UPC Code	037332118684
Brand Compatibility	Powerware; Liebert
BATTERY	
Included Battery Set	Contains (3) 12V 9AH sealed lead acid batteries
Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
PHYSICAL	
Shipping Dimensions (hwd / in.)	6.00 x 7.50 x 11.90



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / cm)	15.24 x 19.05 x 30.23
Shipping Weight (lbs.)	20.00
Shipping Weight (kg)	9.07
Unit Dimensions (hwd / in.)	4.000 x 7.500 x 6.000
Unit Dimensions (hwd / cm)	10.16 x 19.05 x 15.24
Unit Weight (lbs.)	18.6
Unit Weight (kg)	8.44
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
Storage Elevation (ft.)	0 - 50,000
Storage Elevation (m)	0 - 15,200 m
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.