

SmartRack 12-in. (30.48 cm) Width High Capacity Vertical Cable Manager - Double finger duct with cover

MODEL NUMBER: **SRCABLEVRT12**



Highlights

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover
- High capacity (12-in. (30.48 cm) width) for large cable bundles
- Split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Helps eliminate cable stress
- Organizes cables within an Open Rack
- Toolless button mounts
- Cold rolled steel with black finish

Package Includes

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover, mounting hardware

Description

The SmartRack® SRCABLEVRT12 helps eliminate cable stress by organizing the cables within an open rack cabinet. The vertical cable manager (finger duct with cover) is six feet (1.8 meters) high, 12 inches (30.5 centimeters) wide and split into three two-foot (0.6-meter) sections to allow for multiple installation options. SRCABLEVRT12 offers toolless button mounting.

Features

- SmartRack SRCABLEVRT12 helps eliminate cable stress by organizing the cables within an Open Rack cabinet
- The vertical cable manager (finger duct with cover) is 6-ft. (1.83 m) high, 12 inch (30.48 cm) width and split into three 2-ft (0.61 m) sections to allow for multiple installation options
- Toolless button mounting

Specifications

OVERVIEW	
UPC Code	037332161284
Accessory Type	Cable Management Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	4.80 x 25.10 x 26.00
Shipping Dimensions (hwd / cm)	12.19 x 63.75 x 66.04
Shipping Weight (lbs.)	31.30
Shipping Weight (kg)	14.20



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Dimensions (hwd / in.)	24.450 x 12.900 x 6.020
Unit Dimensions (hwd / cm)	62.10 x 32.77 x 15.29
Unit Weight (lbs.)	9.2
Unit Weight (kg)	4.17
Cable Manager Form Factor	Vertical
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.