


SmartRack Copper Bus Grounding Bar for 24U and 25U Racks

MODEL NUMBER: SRGROUND25



Half-length bus grounding bar attaches to your open frame rack or enclosure to provide ground contact for rack-mount equipment.

Features

Provides Convenient Ground Contact for Your Rack-Mounted Equipment

This SmartRack® grounding bar is a thin strip of heavy-gauge solid copper that attaches to any EIA-standard 24U or 25U rack enclosure or open frame rack. Every other U space has a drilled and tapped hole to allow a ground wire jumper to be installed, providing convenient ground contact for standard rack equipment. The jumper then bridges to individual rack components, with grounding straps, allowing a direct path to ground, rather than going through surrounding equipment.

Easy to Install with All Hardware Included

You can mount the SRGROUND25 in any EIA-standard 24U or 25U rack enclosure or open frame rack. Either screw it into a rack enclosure using the included mounting hardware, or install it in an open frame rack with the included toolless mounting buttons. This copper grounding bar is ideal for large data centers that contain ground-sensitive equipment.

Highlights

- Copper grounding bar provides ground contact for your rack-mount equipment
- Installs in your 24U or 25U enclosure or open frame rack with included hardware
- Recommended for large data centers that have ground-sensitive equipment
- Heavy-gauge copper construction with drilled and tapped hole in every other U space

Applications

Provides convenient ground contact for standard rack-mount equipment in a 24U or 25U rack

System Requirements

Fits into any standard 24U or 25U open frame rack or rack enclosure

Package Includes

- Grounding bar with attached lug, 45 in.
- (2) Mounting buttons
- (13) Grounding straps
- (2) M4 self-tapping screws
- (13) M4 screws
- (13) Washers
- (2) Cage nuts
- (2) M6 x 12 screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332241474
Accessory Type	Grounding Bars & Panels
Accessory Class	Rack Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	48.82 x 3.35 x 2.36
Shipping Dimensions (hwd / cm)	124.00 x 8.51 x 5.99
Shipping Weight (lbs.)	4.00



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	1.81
Unit Dimensions (hwd / in.)	45.200 x 0.625 x 0.250
Unit Dimensions (hwd / cm)	114.808 X 1.588 X 0.635
Unit Weight (lbs.)	3.00
Unit Weight (kg)	1.36
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.