

## FC to SC 50/125 OM3 10 Gb Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-SC10G**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an SC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

### Description

The T020-001-SC10G FC to SC 10 Gb Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an SC female port for 50/125 OM3 multimode cable testing. "OM3" is clearly labeled on the unit to differentiate the T020-001-SC10G from other adapters. Included dust caps keep the connectors clean when not in use.

### Features

#### Converts Cable Tester's FC Connector to an SC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 50/125 OM3 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Specifications

OVERVIEW	
UPC Code	037332197627
Technology	Multimode
Optical Mode	OM3
PHYSICAL	
Color	Silver
Clad Diameter (microns)	125

### Highlights

- Converts native FC jack to an SC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 50/125 OM3 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

### System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

### Package Includes

- T020-001-SC10G FC to SC 50/125 OM3 10 Gb Adapter



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Core Diameter (microns)	50
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.