

## USB-C to USB-A Cable (M/M), USB 3.2 Gen 1 (5 Gbps), Thunderbolt 3 Compatible, 20-in. (50.8 cm)

MODEL NUMBER: **U428-20N**



USB-C 3.1 to USB-A cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

### Features

**USB Type-C to USB Type-A Cable Connects a USB-C Mobile Device to a Wall Charger** This 20-inch USB-C 3.1 to USB-A cable allows you to connect any device with a USB-C or Thunderbolt 3 port, including MacBooks, Ultrabooks and Chromebooks, to a USB-enabled computer, charger, hard drive or other peripheral for the purpose of charging, powering, syncing or transferring data. Its 20-inch length makes it easy to carry in your briefcase or laptop bag for quick downloads and file transfers on the go.

**Charges Devices and Transfers Data at Fast USB 3.1 Gen 1 Speeds** The USB-C to USB-A cable supports USB 3.1 Gen 1 data transfer rates up to 5 Gbps, which is 10 times faster than USB 2.0. The Power Delivery cable also provides power output up to 3A (60 watts), which is more than sufficient for charging, syncing and powering compatible devices. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

**Reversible USB-C Connector Attaches in Either Direction** Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

## Specifications

OVERVIEW	
UPC Code	037332243430
Technology	Thunderbolt; USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)

### Highlights

- USB-C to USB-A cable is compatible with all USB-C and Thunderbolt 3 devices
- Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-A wall charger or car charger up to 20 in. away
- Transfer data between an external hard drive or flash drive and your computer or laptop
- Connect your desktop computer to a docking station or hub with a USB-C or Thunderbolt 3 port

### System Requirements

- Device with a USB-C or Thunderbolt 3 port
- Device with a USB-A port
- USB 3.1 Gen 1 compatibility required in both connected devices to achieve USB 3.1 Gen 1 speeds

### Package Includes

- U428-20N USB Type-C to USB Type-A Cable, M/M, 20 in.



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	USB 3.0 A (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
<b>PHYSICAL</b>	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	1.7
Cable Length (m)	0.52
Cable Length (in.)	20
Cable Length (cm)	50.8
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Packaging Type	Polybag
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.1 Gen 1 (up to 5 Gbps)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.