

## Universal Reversible USB 2.0 Converter Adapter Cable (Reversible A to 5Pin Mini B M/M), 3 ft. (0.91 m)

MODEL NUMBER: **UR030-003**



Universal / Reversible "A" connector allows plugging in any direction

### Description

The UR030-003 USB 2.0 Universal / Reversible "A" to Mini-B 5-pin device cable meets or exceeds USB 2.0 specifications. Backward compatible with older USB 1.1 applications as well. USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. The data transfer rates of USB 2.0 (up to 480 Mbps) make them perfect for multimedia applications. Features nickel-plated connectors and gold-plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life..

### Features

- Universal / Reversible "A" connector plugs in any direction
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

## Specifications

| OVERVIEW    |                      |
|-------------|----------------------|
| UPC Code    | 037332179524         |
| Technology  | USB 2.0 (High Speed) |
| Cable Type  | Passive              |
| CONNECTIONS |                      |

### Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

### System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

### Package Includes

- 3-ft. (0.91 m) USB2.0 Universal / Reversible A to Mini-B Device Cable (A Male to 5Pin Mini-B Male)



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                              |
|-------------------------------------|------------------------------|
| Side A - Connector 1                | REVERSIBLE USB A (MALE)      |
| Side B - Connector 1                | USB MINI-B 5-PIN (MALE)      |
| Connector Style                     | Straight                     |
| <b>PHYSICAL</b>                     |                              |
| Cable Jacket Color                  | Black                        |
| Cable Length (ft.)                  | 3                            |
| Cable Length (m)                    | 0.91                         |
| Shipping Dimensions (hwd / in.)     | 0.25 x 0.25 x 8.00           |
| Shipping Dimensions (hwd / cm)      | 0.64 x 0.64 x 20.32          |
| Shipping Weight (lbs.)              | 0.05                         |
| Shipping Weight (kg)                | 0.02                         |
| <b>ENVIRONMENTAL</b>                |                              |
| Operating Temperature Range         | 14° to 122°F (-10° to 50°C)  |
| Storage Temperature Range           | 5° to 140°F (-15° to 60°C)   |
| Operating Humidity Range            | 0% to 90% RH, Non-Condensing |
| Storage Humidity Range              | 0% to 90% RH, Non-Condensing |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                              |
| Product Compliance                  | RoHS                         |
| <b>WARRANTY &amp; SUPPORT</b>       |                              |
| Product Warranty Period (Worldwide) | Lifetime limited warranty    |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.