

## Technical data sheet

### Cable fittings and accessories

---

#### LUTZE TOP-T Locknuts Plastic Plastic NPT, PG and metric



---

#### Identification

|          |                             |
|----------|-----------------------------|
| Type     | TOP-T Locknuts Plastic PG16 |
| Part No. | <a href="#">LPPG16G</a>     |

---

#### Product version

|                   |    |
|-------------------|----|
| Datasheet version | 00 |
|-------------------|----|

---

#### Use/Application/Properties

|            |                                                                                                                                                                 |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Properties | <ul style="list-style-type: none"><li>• Hexagonal locknut for secure tightening of plastic fittings, accessories and cables</li><li>• Easy to install</li></ul> |
|------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|

---

#### Technical data

|                                |                                          |
|--------------------------------|------------------------------------------|
| Temperature range              | -20 °C ... +100 °C<br>-4 °F ... +212 °F  |
| Intermittent temperature range | -40 °C ... +150 °C<br>-40 °F ... +302 °F |
| Outer Ø                        | 33 mm                                    |
| Thread form                    | PG                                       |
| Thread G                       | PG 16                                    |
| SW                             | 30 mm                                    |
| H                              | 6 mm                                     |

---

#### Construction

|          |                                 |
|----------|---------------------------------|
| Material | PA 6 GF 30                      |
| Color    | silver grey similar to RAL 7001 |

---

#### United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park  
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU  
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2  
[www.lutze.com](http://www.lutze.com) • [sales.gb@lutze.co.uk](mailto:sales.gb@lutze.co.uk)

#### Germany: Friedrich Lütze GmbH

Postfach 12 24 (PLZ 71366) • Bruckwiesenstraße 17-19 • D-71384 Weinstadt  
Tel. +49 (0)7151 6053-0 • Fax +49 (0)7151 6053-277(-288)  
[www.luetze.de](http://www.luetze.de) • [info@luetze.de](mailto:info@luetze.de)

18.04.2023 • Subject to technical modification

Part No. [LPPG16G](#) • Datasheet version: 00

## Technical data sheet

### Cable fittings and accessories

#### General

PU (units) 50

#### Notes and Comments

Note Flange is imprinted with locknut size for easy identification.

#### Dimensions

