

DISPLAYPORT2HDMI-C

8in DisplayPort 1.2 Male to HDMI 1.3 Female Black Adapter Cable Which Requires DP++ For Resolution Up to 4K at 30Hz

Features

- DisplayPort 1.2 Male to HDMI 1.3 Female
- 4K at 30Hz Maximum Resolution
- 8in Length
- Black Color PVC Jacket



Product Description

This is an 8in DisplayPort male to HDMI female black adapter cable for connectivity between display devices. The use of this product requires a DP++ output, commonly found in DisplayPort graphics cards. This device offers a maximum resolution of 4K at 30hz. This part is designed to fit your application needs by providing DisplayPort 1.2 to HDMI 1.3 connectivity. Our 100% tested DP to HDMI adapter cables are backed by a 3 year warranty and are guaranteed to work the first time.

Specifications

Parameter	Specifications
Product	DisplayPort to DVI Adapter Cable
Converter Type	Passive
Input Signal	DisplayPort
Output Signal	HDMI
Connector A	DisplayPort (20-Pin) Male
Connector B	HDMI
Resolutions (Maximum)	4K at 30Hz
Color	Black
Cable Material	PVC
Shell Material	ABS
Cable Specification	32AWG, OD 5.0mm
Cable Length	15cm
Product Total Length	20cm

About ProLabs

Our extensive experience comes as standard. For over 20 years ProLabs has delivered optical connectivity solutions that give our customers freedom and choice through our ability to provide seamless interoperability. At the heart of our company is the ability to provide state-of-the-art optical transport and connectivity solutions that are compatible with more than 100 optical switching and transport platforms.

A Complete Portfolio of Network Solutions

ProLabs is focused on innovations in optical transport and connectivity. The combination of our knowledge of optics and networking equipment enables ProLabs to be your single source for optical transport and connectivity solutions from 100Mb to 1.6T while providing innovative solutions that increase network efficiency. We provide the optical connectivity expertise that is compatible with and enhances your switching and transport equipment.

The Trusted Partner

Customer service is our number one value. ProLabs has invested in people, labs and manufacturing capacity to ensure compatible products, and immediate answers to your questions. With Engineering and Manufacturing offices in the U.K. and U.S. augmented by field offices throughout the U.S., U.K. and Asia, ProLabs is able to be our customers best advocate 24 hours a day.



Contact Information

ProLabs US
Email: sales@prolabs.com
Telephone: 952-852-0252

ProLabs UK

Email: salesupport@prolabs.com
Telephone: +44 1285 719 600