



surge suppressor, varistor with LED, 48-127 V AC, 50/60 Hz, 24-70 V DC, for contactors 3RT2.2

product brand name	SIRIUS
product category	Surge suppressor
product designation	Varistor with LED
product type designation	3RT29
suitability for use	for 3RT2.2 contactors
General technical data	
certificate of suitability	CE / UL / CSA
size of contactor	S0
Substance Prohibition (day/month/year)	10/01/2009
SVHC substance name	Lead CAS-No. 7439-92-1
Net Weight	0.005 kg
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
• at 50 Hz rated value	48 ... 127 V
• at 60 Hz rated value	48 ... 127 V
control supply voltage frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
control supply voltage at DC rated value	24 ... 70 V
design of the surge suppressor	Varistor
Ambient conditions	
ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
Installation/ mounting/ dimensions	
mounting position	any
fastening method	clip-on
height	19 mm
width	30 mm
depth	12 mm
Approvals Certificates	
Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	0.0885 kg
• global warming potential [CO2 eq] / during operation	6.96 kg
• global warming potential [CO2 eq] / after end of life	-0.0061 kg
• global warming potential [CO2 eq] / total	7.04 kg
Environment	General Product Approval

[Environmental Con-
firmations](#)



EMV	Test Certificates		Maritime application		
 RCM	Special Test Certificate	Type Test Certificates/Test Report			
Maritime application		other	Railway		
		Confirmation	Miscellaneous		Special Test Certificate

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RT2926-1JK00>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RT2926-1JK00>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RT2926-1JK00>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RT2926-1JK00&lang=en



