



SIMATIC bus adapter: BA LC/RJ45, media converter glass FOC/CU 1x LC FO connection and 1x RJ45 connection

General information	
Product type designation	BA LC/RJ45
HW functional status	from FS04
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch) LC / RJ45
Supports protocol for PROFINET IO	
Number of RJ45 ports	1
Number of LC ports	1; Wavelength of 1 270 ... 1 380 nm, corresponds to 100BASE-FX
Cable length	
— Cu conductors	100 m
— Multimode graded-index fiber 50/125 µm	3 km; min. transmit power -23.5 dB, min. receiver sensitivity -31 dB
— Multimode graded-index fiber 62.5/125 µm	3 km; min. transmit power -20 dB, min. receiver sensitivity -31 dB
Standards, approvals, certificates	
Ecological footprint	
environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	27.1 kg
— global warming potential, (during production) [CO2 eq]	1.35 kg
— global warming potential, (during operation) [CO2 eq]	25.7 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.023 kg
Ambient conditions	
Ambient temperature during operation	
horizontal installation, min.	-30 °C
horizontal installation, max.	60 °C
vertical installation, min.	-30 °C
vertical installation, max.	50 °C
Altitude during operation relating to sea level	
Installation altitude above sea level, max.	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
Dimensions	
Width	20 mm
Height	69.5 mm
Depth	59 mm
Weights	
Weight, approx.	32 g
Classifications	

	Version	Classification
eClass	16	27-24-26-92
eClass	14	27-24-26-92
eClass	12	27-24-26-92
eClass	9.1	27-24-26-92
eClass	9	27-24-26-92
eClass	8	27-24-26-92
eClass	7.1	27-24-26-92
eClass	6	27-24-26-92
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)



General Product Approval

For use in hazardous locations



[CCC-Ex](#)

[FM](#)

For use in hazardous locations

Maritime application



[Miscellaneous](#)

[Type Examination Certificate](#)

[CCC-Ex](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



Maritime application

Environment

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)



last modified:

9/19/2025