

product type designation

product description

7/8 inch connecting cable

Plug-in cable (5-core), preferred length, preassembled with two 5-pole 7/8 inch male/female-contact connectors

7/8" plug-in cable for Power supply of the ET 200, pre-assembled cable with 2 7/8" connectors, 5-pole, 10 m.



product brand name

SIMATIC NET

Technical Product Detail Page

<https://l.siemens.com/1P6XV1822-5BN10>

suitability for use

Power supply of ET 200 modules with 7/8 inch power port to IP 65 degree of protection

cable designation

L-Y11Y-Z 5x1x1.5 GR

wire length

10 m

electrical data

insulation resistance coefficient

1 GΩ·m

operating voltage / RMS value

600 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

16 A; at 25°C (14 A at 40°C)

mechanical data

number of electrical cores

5

type of electrical connection

7/8 inch - 180

outer diameter

• of inner conductor

1.55 mm

• of the wire insulation

2.73 mm

• of cable sheath

10.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

design of stranding element

Pairs

conductor class

5

material

• of the conductor

CU, blank

• of the wire insulation

PVC

• of cable sheath

PUR

product component / PE connection

Yes

marking / of cores

Color, digits

color

• of the power line insulation

black

• of cable sheath

gray

bending radius

• with single bend / minimum permissible

27 mm

• with multiple bends / minimum permissible

63 mm

• with continuous bending

75 mm

number of bending cycles

5000000; For use in cable carriers, for 5 million bending cycles with a bending radius of 75 mm, an acceleration of 4 m/s² and a speed of 180 m/min

tensile load / maximum

500 N

weight per length	149 kg/km
plug	
type of plug interlock	screwed
design of plug-in connection	7/8 inch - 180
connector coding	7/8 inch
ambient conditions	
ambient temperature	
• during operation	-40 ... +80 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
• during installation	-40 ... +80 °C
fire behavior	Flame-resistant acc. to IEC 60332-1
chemical resistance	
• to mineral oil	resistant
• to grease	resistant
radiological resistance / to UV radiation	resistant
protection class IP	IP65 / 67
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	Yes
certificate of suitability	UL2238 E300110
• EAC approval	Yes
• RoHS conformity	Yes
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors	https://support.industry.siemens.com/cs/ww/en/view/109766358
• to web page: selection aid TIA Selection Tool	https://www.siemens.com/tstcloud
• to website: Industrial communication	https://www.siemens.com/simatic-net
• to web page: SiePortal	https://sieportal.siemens.com/
• to website: Image database	https://www.automation.siemens.com/bilddb
• to website: CAX-Download-Manager	https://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
security information	
security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry . Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert . (V4.7)
Approvals / Certificates	
General Product Approval	



[Declaration of Con-
formity](#)



[Manufacturer Declara-
tion](#)

[China RoHS](#)



[Miscellaneous](#)

[PROFINET](#)

last modified:

5/9/2026 