



Figure similar

Contact block and lampholder 1 NC, 1 NC, Wedge base W2 x 4.6 d, soldering pin connection

product brand name	SIRIUS
product designation	contact block and lampholder
product type designation	3SB2
Contact block/ lampholder	
socket design	W2 x 4.6d
number of lampholders	1
General technical data	
product function positive opening	Yes
product component	
• light source	No
suitability for integration	pushbutton / selector button
type of voltage	
• of the operating voltage	AC/DC
protection class IP	
• of the enclosure	IP40
• of the terminal	IP00
vibration resistance according to IEC 60068-2-6	20 ... 200 Hz: 5 g
reference code according to IEC 81346-2	S
Substance Prohibitance (day/month/year)	07/01/2006
Net Weight	5.988 g
operating voltage	
• at AC	
— at 50 Hz rated value	5 ... 60 V
— at 60 Hz rated value	5 ... 60 V
• at DC rated value	5 ... 60 V
Auxiliary circuit	
number of NC contacts for auxiliary contacts	2
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
operational current at AC-12	
• at 24 V rated value	10 A
• at 60 V rated value	10 A
• at 110 V rated value	10 A
• at 230 V rated value	10 A
operational current at AC-15	
• at 24 V rated value	4 A
• at 110 V rated value	4 A
• at 230 V rated value	4 A

operational current at DC-12	
• at 24 V rated value	6 A
• at 60 V rated value	5 A
• at 110 V rated value	2.5 A
• at 230 V rated value	1 A
operational current at DC-13	
• at 24 V rated value	3 A
• at 60 V rated value	1.2 A
• at 110 V rated value	0.7 A
• at 230 V rated value	0.3 A

Connections/ Terminals

type of electrical connection	solder pin connectors
--------------------------------------	-----------------------

Ambient conditions

ambient temperature	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C

Installation/ mounting/ dimensions

fastening method	clip-on
height	19 mm
width	18 mm
depth	29 mm

Approvals Certificates

Environment	General Product Approval
--------------------	--------------------------

[Environmental Con-
firmations](#)



other

[Confirmation](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2455-1F>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2455-1F>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2455-1F>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2455-1F&lang=en

last modified:

4/4/2026