

Label holder, flat, Frame rounded off at the bottom, black, for labeling plate 27mm x 27mm for snapping on, Z=100-unit packaging

product brand name	SIRIUS ACT		
product designation	Label holder		
design of the product	for labeling plate 27 x 27 mm		
product type designation	3SU1		
General technical data			
protection class IP	IP66, IP67, IP69(IP69K)		
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12		
shock resistance for railway applications according to EN 61373	Category 1, Class B		
vibration resistance for railway applications according to EN 61373	Category 1, Class B		
Substance Prohibittance (Date)	03/01/2017		
Weight	3 g		
Ambient conditions			
ambient temperature			
• during operation	70 ... -25 °C		
• during storage and transport	80 ... -40 °C		
Environmental footprint			
Environmental Product Declaration(EPD)	Yes		
global warming potential [CO2 eq] total	0.787 kg		
global warming potential [CO2 eq] during manufacturing	0.566 kg		
global warming potential [CO2 eq] during operation	0.235 kg		
global warming potential [CO2 eq] after end of life	-0.015 kg		
Installation/ mounting/ dimensions			
height	59.8 mm		
width	29.8 mm		
Accessories			
material of accessory	Plastic		
shape of label holder	rounded below		
color of label holder	Black		
fastening method of label	snap on		
Approvals Certificates			
General Product Approval		Test Certificates	Maritime application



[Type Test Certificates/Test Report](#)



Maritime application	other	Environment
----------------------	-------	-------------



[Confirmation](#)



Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0AT10-0AA0-Z X90>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0AT10-0AA0-Z X90>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0AT10-0AA0-Z X90>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0AT10-0AA0-Z X90&lang=en



last modified:

4/2/2025