

labeling plate for snapping on or gluing on label holder, label size 12.5 x 27 mm, black label, white font, with inscription: Fermé



product brand name		SIRIUS ACT
product designation		Labeling plate
product type designation		3SU1
General technical data		
protection class IP		IP66, IP67, IP69(IP69K)
shock resistance for railway applications according to EN 61373		Category 1, Class B
vibration resistance for railway applications according to EN 61373		Category 1, Class B
Substance Prohibittance (Date)		10/01/2014
Weight		1 g
Ambient conditions		
ambient temperature		
• during operation		70 ... -25 °C
• during storage and transport		80 ... -40 °C
Environmental footprint		
Environmental Product Declaration(EPD)		Yes
global warming potential [CO2 eq] total		0.787 kg
global warming potential [CO2 eq] during manufacturing		0.566 kg
global warming potential [CO2 eq] during operation		0.235 kg
global warming potential [CO2 eq] after end of life		-0.015 kg
Installation/ mounting/ dimensions		
height		12.5 mm
width		27 mm
Accessories		
material of accessory		Plastic
fastening method of label		snap on / stick
marking of the name plate for command devices		Fermé
shape of the name plate for command devices		rectangular
color of the label		black (plate); white (text)
Approvals Certificates		
General Product Approval		Test Certificates
		Maritime application
 EG-Konf.   cULus  Type Test Certificates/Test Report  LRS		
Maritime application		Environment
other		



[Confirmation](#)



Environment

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0AC16-0GK0>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0AC16-0GK0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0AC16-0GK0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0AC16-0GK0&lang=en



last modified:

4/2/2025