



Washer for EMERGENCY STOP, yellow, with inscription (Polish): Zatrzymanie symbol 5638, Awaryjne symbol 5638, outer diameter 75 mm, Inside diameter 22.5 mm, Thickness 2 mm

product brand name	SIRIUS ACT		
product designation	EMERGENCY STOP plate		
product type designation	3SU1		
General technical data			
shock resistance for railway applications according to EN 61373	Category 1, Class B		
vibration resistance for railway applications according to EN 61373	Category 1, Class B		
Substance Prohibittance (Date)	10/01/2014		
Net Weight	7 g		
Ambient conditions			
ambient temperature			
• during operation	70 ... -25 °C		
• during storage and transport	80 ... -40 °C		
Environmental footprint			
Environmental Product Declaration(EPD)	Yes		
global warming potential [CO2 eq] total	0.787 kg		
global warming potential [CO2 eq] during manufacturing	0.566 kg		
global warming potential [CO2 eq] during operation	0.235 kg		
global warming potential [CO2 eq] after end of life	-0.015 kg		
Accessories			
material of accessory	Plastic		
fastening method of label	without		
marking of backing plate	ZATRZYMANIE, SYMBOL IEC 60417-5638, AWARYJNE, SYMBOL IEC 60417-5638		
shape of backing plate	Round		
color of backing plate	yellow (plate); black (text)		
product function illuminated backing plate	No		
printed ISO symbols	ZATRZYMANIE, SYMBOL IEC 60417-5638 , AWARYJNE, SYMBOL IEC 60417-5638		
Approvals Certificates			
General Product Approval		Test Certificates	Maritime application



[Type Test Certificates/Test Report](#)



Maritime application	other	Environment
----------------------	-------	-------------



[Confirmation](#)



Environment

Siemens
EcoTech



[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1900-0BB31-0ND0>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1900-0BB31-0ND0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1900-0BB31-0ND0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1900-0BB31-0ND0&lang=en



last modified:

4/2/2025