



stand-alone assembly support for 3RU21/3RB30/3RB31/3RR2 Size S00 Stand-alone installation Main circuit: Spring-type terminal Auxiliary circuit: --

product brand name		SIRIUS
product category		Terminal support
product designation		individual mount
product type designation		3RU29
General technical data		
size of overload relay		S00
protection class IP on the front • according to IEC 60529		IP20
Substance Prohibittance (Date)		10/01/2009
Net Weight		0.06 kg
Ambient conditions		
ambient temperature • during operation • during storage		-20 ... +70 °C -50 ... +80 °C
Electrical Safety		
protection class IP on the front according to IEC 60529		IP20
touch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front
Installation/ mounting/ dimensions		
fastening method		screw and snap-on mounting onto 35 mm DIN rail
height		102 mm
width		45 mm
depth		68 mm
Connections/ Terminals		
type of electrical connection • for main current circuit		spring-loaded terminals
type of connectable conductor cross-sections • for main contacts — solid — stranded — finely stranded with core end processing • for AWG cables for main contacts		1x (0.5 ... 4 mm²) 1x (0,5 ... 4 mm²) 0.5 ... 2.5 mm² 1x (20 ... 12)
Approvals Certificates		
Environment	General Product Approval	Test Certificates

[Environmental Confirmations](#)



[Type Test Certificates/Test Report](#)

Test Certificates	Maritime application
-------------------	----------------------

[Special Test Certificate](#)



Maritime application	other
----------------------	-------



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RU2916-3AC01>

Cax online generator


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RU2916-3AC01>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RU2916-3AC01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RU2916-3AC01&lang=en





1/L1

3/L2

5/L3

last modified:

4/2/2025 