



Electronic remote reset 24...30 V AC/DC for 3RU Size S00...S3

product brand name		SIRIUS							
product category		Reset modules							
product designation		Electric reset							
design of the product		Electrical Remote RESET							
product type designation		3RU19							
General technical data									
size of overload relay		S00, S0, S2, S3							
Substance Prohibittance (Date)		07/01/2006							
Net Weight		0.055 kg							
type of voltage of the control supply voltage		AC/DC							
control supply voltage 1 at AC									
• at 50 Hz		24 ... 30 V							
• at 60 Hz		24 ... 30 V							
control supply voltage frequency									
• 1 rated value		50 Hz							
• 2 rated value		60 Hz							
control supply voltage 1 at DC		24 ... 30 V							
Ambient conditions									
ambient temperature									
• during operation		-20 ... +70 °C							
• during storage		-50 ... +80 °C							
Connections/ Terminals									
type of electrical connection for auxiliary and control circuit		screw-type terminals							
connectable conductor cross-section for auxiliary contacts									
• solid or stranded		0.5 ... 2.5 mm²							
• finely stranded with core end processing		0.5 ... 2.5 mm²							
type of connectable conductor cross-sections for auxiliary contacts									
• solid		2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)							
• finely stranded with core end processing		2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)							
Approvals Certificates									
Environment		General Product Approval		Test Certificates					
Environmental Con- firmations		 EG-Konf.		  UL				Type Test Certifi- cates/Test Report	
Test Certificates		Maritime application				other			



other

Railway

[Confirmation](#)

[Special Test Certificate](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RU1900-2AB71>

Cax online generator



<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RU1900-2AB71>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RU1900-2AB71>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RU1900-2AB71&lang=en





last modified:

4/2/2025 