



Figure similar

Molded-plastic enclosure for surface mounting Degree of protection IP55 with N and PE terminal Can be locked in O position 72 mm with metric cable gland No UL/CSA approval

|                          |                                               |
|--------------------------|-----------------------------------------------|
| product brand name       | SIRIUS                                        |
| product category         | Enclosure                                     |
| product designation      | Molded-plastic enclosure for surface mounting |
| design of the product    | Assembly                                      |
| product type designation | 3RV19                                         |

General technical data

|                                         |            |
|-----------------------------------------|------------|
| product function EMERGENCY OFF function | No         |
| protection class IP of the enclosure    | IP55       |
| Substance Prohibittance (Date)          | 07/01/2006 |
| Net Weight                              | 0.338 kg   |
| material of the enclosure               | plastic    |

Installation/ mounting/ dimensions

|        |        |
|--------|--------|
| height | 155 mm |
| width  | 105 mm |
| depth  | 126 mm |

Approvals Certificates

|                          |                   |                      |
|--------------------------|-------------------|----------------------|
| General Product Approval | Test Certificates | Maritime application |
|--------------------------|-------------------|----------------------|



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



|                      |       |         |
|----------------------|-------|---------|
| Maritime application | other | Railway |
|----------------------|-------|---------|



[Confirmation](#)

[Miscellaneous](#)



[Special Test Certificate](#)

|             |
|-------------|
| Environment |
|-------------|

[Environmental Confirmations](#)

|                     |
|---------------------|
| Further information |
|---------------------|

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information for data generation and storage**

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV1923-1DA00>

**Cax online generator**


<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV1923-1DA00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3RV1923-1DA00>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RV1923-1DA00&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV1923-1DA00&lang=en)



last modified:

10/18/2025